



**OPULENT  
SUPPORT**

Avenida do Município da Ribeira Grande  
Lote 87, R/C - Esq.  
2350-088 Torres Novas - Portugal

Rua dos Amendoais,  
Lote 3, Armazém 1  
8365-235 Tunes - Portugal



Tel: 249821277

Whatsapp: 912518638

Mail: [comercial@opulentsupport.pt](mailto:comercial@opulentsupport.pt)


Web: [www.opulentsupport.pt](http://www.opulentsupport.pt)




## EXS<sup>®</sup> Dental Unit

The EXS<sup>®</sup> Dental Unit includes

- Foot Switch for speed control and water activation.
- 3-way air water syringe (air, water and mist).
- High speed handpiece with advanced LED illumination.
- Low speed air motor handpiece system with 1:1 straight attachment for restorative dental attachments and contra angle attachment for prophylaxis.
- Built-in LED Piezo scaler with accessory kit.
- High power suction system with built-in saline pump.
- Water bottle assembly.
- Quiet and low maintenance oil-free air compressor.



Order No. 102DVET



Easy-to-clean silicone mat and magnetic bur holder keep your workspace tidy and prevent accidental drops.



Intuitive Operation with clearly labeled easy-to-use controls.



## Included

Description	Qty
High Speed LED HP	1 pcs
Low Speed Attachment	2 pcs
3-way Air/Water Syringe	1 pcs
Suction System	1 pcs
Disposable Saliva Ejector	1 set (20pcs)
LED Piezo Scaler	1 set
Scaler Tips	3 pcs (Universal*2+Chisel*1)
Prophy Cup/Brush (Latch)	12 pcs each type
Abrasive Polishing Agent	1 btl
High Speed Bur	30 pcs



LED Piezo Scaler Handpiece

Order No. 173H

Straight Attachment

Order No. 166S

Contra Angle Attachment

Order No. 166CA

Low Speed Air Motor Connector

Order No. Z169M

High Speed LED Handpiece

Order No. Z235

High Speed LED Handpiece Connector

Order No. Z236

## SPECIFICATIONS of UNIT

Input	AC 220V 50/60Hz
Output power consumption	750W
Size	L450 x W600 x H840~940 mm
Weight	42KG

Ultrasonic Scaler Frequency	27,000 to 32,000 Hz
Low speed Attachment speed (Straight, Contra Angle)	30,000 r.p.m.
High speed LED HP speed	380,000 r.p.m.
Compressor Tank Capacity	8L

**Apixia Corporation** Company Address: 7F-1, 128, Sec.2, Dunhua S. Rd., Da-An Dist., Taipei City Taiwan R.O.C.  
Office: +886-2-2702-2608 Fax: +886-2-27554919 Email: vet@apixia.asia www.apixiavet.com

**Apixia Inc.** Company Address: 18688 San Jose Ave. Industry, CA 91748 USA  
Office: +1-626-810-9201 Fax: +1-626-810-9207 Email: info@apixia.com www.apixiavet.com

**Apixia Japan** Company Address: 1324, Ooida, Daian-cho, Inabe-shi, Mie-ken 511-0274, Japan  
Office: +81-0594-41-3080 Fax: +81-0594-41-3081 Email: sale3@apixia.asia www.apixiavet.com

**Apixia Europe**  
Office: +32-5831-7464 Mobile: +32-4739-37167 Email: pascal@apixia.com www.apixiavet.com